


Sub-Enamel Illumination

LUM G2

Fast Caries
Detection
for IRIS 2.0

Now with detaching
autoclavable tip.

This next generation LUM G2 uses powerful sub-enamel illumination for caries detection.



Works in over 40
software programs.



The LUM's specialized LED technology applies a high-intensity light source traveling perpendicular to the plane of the tooth. When a tooth has impurities such as fractures or leaking amalgam, the light is dispersed showing up clearly in near X-ray like images.

FDA registered and approved.

1-800-518-1102
www.digi-doc.com

 **Digital DOC**